

# UCCONNECT®

## UC9500 Light Weight Fibre Suite




### UC 1U Patch Panel 9510, Fixed type, Empty

- Light weight
- Sleek design & feel
- Water paint
- Easy fixtures
- Abrasion resistance
- Highly durable
- Easy fix-up to 4 module cassettes
- Easy fix-up to 4 adaptor panels
- Up to 96 fibres (MPO configuration)

### Specification


Item	Description
Material	Steel
Matrix	Thickness = 1.2 mm
Cover	Thickness = 1.2 mm
Dimension	H x W x D = 1U x 482 mm x 300 mm
Weight	Approximate 3.26 kg (empty)
Surface Finishing	Water painting

### Construction




## UCCONNECT<sup>®</sup> UC9500 Light Weight Fibre Suite

Configuration illustration:



Real-life Configuration:




## UCCONNECT<sup>®</sup>

### UC9500 Light Weight Fibre Suite

#### Ordering Information

SAP1C		Material Description	Weight	Items per Packaging Unit
TBA	PP9510	UC9500 1U Fibre Distribution Modular Panel, 4 Slot, Empty, Flat	3260g	1
<b>Related Products</b>				
TBA	TBA	Blank insert for PP9510		1
TBA	PPMT9541-A12	UC9500 Module MTP-Duplex LC 12F G657A2 BendBright Blue Type A	550g	1
TBA	PPMP9541-A12	UC9500 Module MPO-Duplex LC 12F G657A2 BendBright Blue Type A	550g	1
TBA	PPMT9542-A24	UC9500 Module MTP-Duplex LC 24F G657A2 BendBright Blue Type A	550g	1
TBA	PPMP9542-A24	UC9500 Module MPO-Duplex LC 24F G657A2 BendBright Blue Type A	550g	1
TBA	PPMT9551-A12	UC9500 Module MTP-Duplex LC 12F OM4 BendBright Violet Type A	550g	1
TBA	PPMP9551-A12	UC9500 Module MPO-Duplex LC 12F OM4 BendBright Violet Type A	550g	1
TBA	PPMT9552-A24	UC9500 Module MTP-Duplex LC 24F OM4 BendBright Violet Type A	550g	1
TBA	PPMP9552-A24	UC9500 Module MPO-Duplex LC 24F OM4 BendBright Violet Type A	550g	1
TBA	PPMT9561-A12	UC9500 Module MTP-Duplex LC 12F OM3 BendBright Aqua Type A	550g	1
TBA	PPMP9561-A12	UC9500 Module MPO-Duplex LC 12F OM3 BendBright Aqua Type A	550g	1
TBA	PPMT9562-A24	UC9500 Module MTP-Duplex LC 24F OM3 BendBright Aqua Type A	550g	1
TBA	PPMP9562-A24	UC9500 Module MPO-Duplex LC 24F OM3 BendBright Aqua Type A	550g	1
YMMBP02064	PPMT9541-12	UC9500 Module MTP-Duplex LC 12F G657A2 BendBright Blue Type B	550g	1
YMMBP02065	PPMP9541-12	UC9500 Module MPO-Duplex LC 12F G657A2 BendBright Blue Type B	550g	1
YMMBP02066	PPMT9542-24	UC9500 Module MTP-Duplex LC 24F G657A2 BendBright Blue Type B	550g	1
YMMBP02067	PPMP9542-24	UC9500 Module MPO-Duplex LC 24F G657A2 BendBright Blue Type B	550g	1
YMMBP02070	PPMT9551-12	UC9500 Module MTP-Duplex LC 12F OM4 BendBright Violet Type B	550g	1
YMMBP02071	PPMP9551-12	UC9500 Module MPO-Duplex LC 12F OM4 BendBright Violet Type B	550g	1
YMMBP02072	PPMT9552-24	UC9500 Module MTP-Duplex LC 24F OM4 BendBright Violet Type B	550g	1
YMMBP02073	PPMP9552-24	UC9500 Module MPO-Duplex LC 24F OM4 BendBright Violet Type B	550g	1
YMMBP02076	PPMT9561-12	UC9500 Module MTP-Duplex LC 12F OM3 BendBright Aqua Type B	550g	1
YMMBP02077	PPMP9561-12	UC9500 Module MPO-Duplex LC 12F OM3 BendBright Aqua Type B	550g	1
YMMBP02078	PPMT9562-24	UC9500 Module MTP-Duplex LC 24F OM3 BendBright Aqua Type B	550g	1
YMMBP02079	PPMP9562-24	UC9500 Module MPO-Duplex LC 24F OM3 BendBright Aqua Type B	550g	1
	PPA9514-6-LC-OM4	UC9500 1 Slot 6 Port LC Duplex Front Panel with 6 D532020V adaptors		
	PPST9521-C	UC9500 Splice Tray Cover		
	PPST9521-24	UC9500 Splice Tray 24F		

## UCCONNECT® UC9500 Light Weight Fibre Suite




### UC 1U Patch Panel 9515, Drawer type, Empty


- Light weight
- Sleek design & feel
- Water paint
- Drawer for easy installation and maintenance
- Abrasion resistance
- Highly durable
- Easy fix-up to 4 module cassettes
- Easy fix-up to 4 adaptor panels
- Up to 96 fibres (MPO configuration)

## Specification

Item	Description
Material	SPCC (Cold rolled steel plate)
Matrix	Thickness = 1.2 mm
Cover	Thickness = 1.2 mm
Dimension	H x W x D = 1U x 482 mm x 300 mm
Weight	Approximate 4 kg (empty)
Surface Finishing	Powder paint


## Construction






## Configuration

### Splicing Configuration (48F FC Adaptors):



## MPO Configuration:



## Ordering Information

SAP1C	Material Description	Weight	Items per Packaging Unit
TBA      PPA9515	UC9500 1U Fibre Distribution Modular Panel, 4 Slot, Empty, Drawer	4000g	1
<b>Related Products</b>			
TBA      PPA9515-0	UC9500 1U 1 Slot Blank Front Panel	40g	8
YAPBP02645      PPA9514-6	UC9500 1 Slot 6-Port LC Duplex/SC Simplex Front Panel, Empty	28g	8
TBA      PPA9514-6LCSM	UC9500 1 Slot 6-Port LC Duplex Front Panel with 6 SM adaptors	37g	4
TBA      PPA9514-6LCM2	UC9500 1 Slot 6-Port LC Duplex Front Panel with 6 OM1 & OM2 adaptors	37g	4
TBA      PPA9514-6LCM3	UC9500 1 Slot 6-Port LC Duplex Front Panel with 6 OM3 adaptors	37g	4
TBA      PPA9514-6LCM4	UC9500 1 Slot 6-Port LC Duplex Front Panel with 6 OM4 adaptors	37g	4
TBA      PPA9514-6SCSM	UC9500 1 Slot 6-Port SC Simplex Front Panel with 6 SM adaptors	37g	4
TBA      PPA9514-6SCM2	UC9500 1 Slot 6-Port SC Simplex Front Panel with 6 OM1 & OM2 adaptors	37g	4
TBA      PPA9514-6SCM3	UC9500 1 Slot 6-Port SC Simplex Front Panel with 6 OM3 adaptors	37g	4
TBA      PPA9514-6SCM4	UC9500 1 Slot 6-Port SC Simplex Front Panel with 6 OM4 adaptors	37g	4
TBA      PPA9511-6	UC9500 1 Slot 6-Port SC Duplex Front Panel, Empty	28g	8
TBA      PPA9511-6SM	UC9500 1 Slot 6-Port SC Duplex Front Panel with 6 SM adaptors	52g	4

TBA	PPA9511-6M2	UC9500 1 Slot 6-Port SC Duplex Front Panel with 6 OM1 & OM2 adaptors	52g	4
TBA	PPA9511-6M3	UC9500 1 Slot 6-Port SC Duplex Front Panel with 6 OM3 adaptors	52g	4
TBA	PPA9511-6M4	UC9500 1 Slot 6-Port SC Duplex Front Panel with 6 OM4 adaptors	52g	4
TBA	PPA9512-6	UC9500 1 Slot 6-Port ST Simplex Front Panel, Empty	32g	8
TBA	PPA9512-6SM	UC9500 1 Slot 6-Port ST Simplex Front Panel with 6 SM adaptors	77g	4
TBA	PPA9512-6MM	UC9500 1 Slot 6-Port ST Simplex Front Panel with 6 MM adaptors	77g	4
TBA	PPA9513-6	UC9500 1 Slot 6-Port FC Simplex Front Panel, Empty	32g	8
TBA	PPA9513-6SM	UC9500 1 Slot 6-Port FC Simplex Front Panel with 6 SM adaptors	90g	4
TBA	PPA9513-6MM	UC9500 1 Slot 6-Port FC Simplex Front Panel with 6 MM adaptors	90g	4
TBA	PPA9513-12	UC9500 1 Slot 12-Port FC Simplex Front Panel, Empty	25g	8
TBA	PPA9513-12SM	UC9500 1 Slot 12-Port FC Simplex Front Panel with 12 SM adaptors	142g	4
TBA	PPA9513-12SA	UC9500 1 Slot 12-Port FC Simplex Front Panel with 12 SM APC adaptors	142g	4
TBA	PPA9513-12MM	UC9500 1 Slot 12-Port FC Simplex Front Panel with 12 MM adaptors	142g	4
YFTBP02647	PPST9521-C	UC9500 Splice Tray Cover	29g	1
YFTBP02646	PPST9521-24	UC9500 Splice Tray 24F	43g	2
TBA	PPMT9541-P12	UC9500 Module MTP-Duplex LC 12F G657A2 BendBright Blue Type P	142g	1
TBA	PPMP9541-P12	UC9500 Module MPO-Duplex LC 12F G657A2 BendBright Blue Type P	142g	1
TBA	PPMT9542-P24	UC9500 Module MTP-Duplex LC 24F G657A2 BendBright Blue Type P	142g	1
TBA	PPMP9542-P24	UC9500 Module MPO-Duplex LC 24F G657A2 BendBright Blue Type P	142g	1
TBA	PPMT9561-P12	UC9500 Module MTP-Duplex LC 12F OM3 BendBright Aqua Type P	142g	1
TBA	PPMP9561-P12	UC9500 Module MPO-Duplex LC 12F OM3 BendBright Aqua Type P	142g	1
TBA	PPMT9562-P24	UC9500 Module MTP-Duplex LC 24F OM3 BendBright Aqua Type P	142g	1
TBA	PPMP9562-P24	UC9500 Module MPO-Duplex LC 24F OM3 BendBright Aqua Type P	142g	1
TBA	PPMT9551-P12	UC9500 Module MTP-Duplex LC 12F OM4 BendBright Violet Type P	142g	1
TBA	PPMP9551-P12	UC9500 Module MPO-Duplex LC 12F OM4 BendBright Violet Type P	142g	1
TBA	PPMT9552-P24	UC9500 Module MTP-Duplex LC 24F OM4 BendBright Violet Type P	142g	1
TBA	PPMP9552-P24	UC9500 Module MPO-Duplex LC 24F OM4 BendBright Violet Type P	142g	1

# UCCONNECT®

## UC9500 Light Weight Fibre Suite




### UC 2U Patch Panel 9520, Fixed type, Empty

- Light weight
- Sleek design & feel
- Water paint
- Easy fixtures
- Abrasion resistance
- Highly durable
- Easy fix-up to 8 module cassettes
- Easy fix-up to 8 adaptor panels
- Up to 192 fibres (MPO configuration)

## Specification

Item	Description
Material	Steel
Matrix	Thickness = 1.2 mm
Cover	Thickness = 1.2 mm
Dimension	H x W x D = 2U x 482 mm x 300 mm
Weight	Approximate 6.52 kg (empty)
Surface Finishing	Water painting


## Construction





## UCCONNECT® UC9500 Light Weight Fibre Suite

Configuration illustration:



Real-life Configuration:




# UCCONNECT<sup>®</sup>

## UC9500 Light Weight Fibre Suite

### Ordering Information

SAP1C		Material Description	Weight	Items per Packaging Unit
TBA	PP9520	UC9500 2U Fibre Distribution Modular Panel, 8 Slot, Empty, Flat	6520g	1
<b>Related Products</b>				
TBA	TBA	Blank insert for PP9510		1
TBA	PPMT9541-A12	UC9500 Module MTP-Duplex LC 12F G657A2 BendBright Blue Type A	550g	1
TBA	PPMP9541-A12	UC9500 Module MPO-Duplex LC 12F G657A2 BendBright Blue Type A	550g	1
TBA	PPMT9542-A24	UC9500 Module MTP-Duplex LC 24F G657A2 BendBright Blue Type A	550g	1
TBA	PPMP9542-A24	UC9500 Module MPO-Duplex LC 24F G657A2 BendBright Blue Type A	550g	1
TBA	PPMT9551-A12	UC9500 Module MTP-Duplex LC 12F OM4 BendBright Violet Type A	550g	1
TBA	PPMP9551-A12	UC9500 Module MPO-Duplex LC 12F OM4 BendBright Violet Type A	550g	1
TBA	PPMT9552-A24	UC9500 Module MTP-Duplex LC 24F OM4 BendBright Violet Type A	550g	1
TBA	PPMP9552-A24	UC9500 Module MPO-Duplex LC 24F OM4 BendBright Violet Type A	550g	1
TBA	PPMT9561-A12	UC9500 Module MTP-Duplex LC 12F OM3 BendBright Aqua Type A	550g	1
TBA	PPMP9561-A12	UC9500 Module MPO-Duplex LC 12F OM3 BendBright Aqua Type A	550g	1
TBA	PPMT9562-A24	UC9500 Module MTP-Duplex LC 24F OM3 BendBright Aqua Type A	550g	1
TBA	PPMP9562-A24	UC9500 Module MPO-Duplex LC 24F OM3 BendBright Aqua Type A	550g	1
YMMBP02064	PPMT9541-12	UC9500 Module MTP-Duplex LC 12F G657A2 BendBright Blue Type B	550g	1
YMMBP02065	PPMP9541-12	UC9500 Module MPO-Duplex LC 12F G657A2 BendBright Blue Type B	550g	1
YMMBP02066	PPMT9542-24	UC9500 Module MTP-Duplex LC 24F G657A2 BendBright Blue Type B	550g	1
YMMBP02067	PPMP9542-24	UC9500 Module MPO-Duplex LC 24F G657A2 BendBright Blue Type B	550g	1
YMMBP02070	PPMT9551-12	UC9500 Module MTP-Duplex LC 12F OM4 BendBright Violet Type B	550g	1
YMMBP02071	PPMP9551-12	UC9500 Module MPO-Duplex LC 12F OM4 BendBright Violet Type B	550g	1
YMMBP02072	PPMT9552-24	UC9500 Module MTP-Duplex LC 24F OM4 BendBright Violet Type B	550g	1
YMMBP02073	PPMP9552-24	UC9500 Module MPO-Duplex LC 24F OM4 BendBright Violet Type B	550g	1
YMMBP02076	PPMT9561-12	UC9500 Module MTP-Duplex LC 12F OM3 BendBright Aqua Type B	550g	1
YMMBP02077	PPMP9561-12	UC9500 Module MPO-Duplex LC 12F OM3 BendBright Aqua Type B	550g	1
YMMBP02078	PPMT9562-24	UC9500 Module MTP-Duplex LC 24F OM3 BendBright Aqua Type B	550g	1
YMMBP02079	PPMP9562-24	UC9500 Module MPO-Duplex LC 24F OM3 BendBright Aqua Type B	550g	1

## UCCONNECT® UC9500 Light Weight Fibre Suite




### UC 4U Patch Panel 9540, Drawer type, Empty

- Light weight
- Sleek design & feel
- Water paint
- Drawer for easy installation and maintenance
- Abrasion resistance
- Highly durable
- Easy fix-up to 12 module cassettes
- Easy fix-up to 12 adaptor panels
- Up to 288 fibres (MPO configuration and LC Quad)

## Specification


Item	Description
Material	Steel
Matrix	Thickness = 1.2 mm
Cover	Thickness = 1.2 mm
Dimension	H x W x D = 4U x 482 mm x 452 mm
Weight	Approximate 6 kg (empty)
Surface Finishing	Water painting

## Construction




## Configuration

### Splicing Configuration:



## MPO Configuration:



## Ordering Information

SAP1C	Material Description	Weight	Items per Packaging Unit
TBA	PP9540 UC9500 4U Fibre Distribution Modular Panel, 12 Slot, Empty, Drawer	6000g	1
<b>Related Products</b>			
TBA	PPA9515-0 UC9500 1U 1 Slot Blank Front Panel	40g	8
YAPBP02645	PPA9514-6 UC9500 1 Slot 6-Port LC Duplex/SC Simplex Front Panel, Empty	28g	8
TBA	PPA9514-6LCSM UC9500 1 Slot 6-Port LC Duplex Front Panel with 6 SM adaptors	37g	4
TBA	PPA9514-6LCM2 UC9500 1 Slot 6-Port LC Duplex Front Panel with 6 OM1 & OM2 adaptors	37g	4
TBA	PPA9514-6LCM3 UC9500 1 Slot 6-Port LC Duplex Front Panel with 6 OM3 adaptors	37g	4
TBA	PPA9514-6LCM4 UC9500 1 Slot 6-Port LC Duplex Front Panel with 6 OM4 adaptors	37g	4
TBA	PPA9514-6SCSM UC9500 1 Slot 6-Port SC Simplex Front Panel with 6 SM adaptors	37g	4
TBA	PPA9514-6SCM2 UC9500 1 Slot 6-Port SC Simplex Front Panel with 6 OM1 & OM2 adaptors	37g	4
TBA	PPA9514-6SCM3 UC9500 1 Slot 6-Port SC Simplex Front Panel with 6 OM3 adaptors	37g	4
TBA	PPA9514-6SCM4 UC9500 1 Slot 6-Port SC Simplex Front Panel with 6 OM4 adaptors	37g	4
TBA	PPA9511-6 UC9500 1 Slot 6-Port SC Duplex Front Panel, Empty	28g	8
TBA	PPA9511-6SM UC9500 1 Slot 6-Port SC Duplex Front Panel with 6 SM adaptors	52g	4
TBA	PPA9511-6M2 UC9500 1 Slot 6-Port SC Duplex Front Panel with 6 OM1 & OM2 adaptors	52g	4

TBA	PPA9511-6M3	UC9500 1 Slot 6-Port SC Duplex Front Panel with 6 OM3 adaptors	52g	4
TBA	PPA9511-6M4	UC9500 1 Slot 6-Port SC Duplex Front Panel with 6 OM4 adaptors	52g	4
TBA	PPA9512-6	UC9500 1 Slot 6-Port ST Simplex Front Panel, Empty	32g	8
TBA	PPA9512-6SM	UC9500 1 Slot 6-Port ST Simplex Front Panel with 6 SM adaptors	77g	4
TBA	PPA9512-6MM	UC9500 1 Slot 6-Port ST Simplex Front Panel with 6 MM adaptors	77g	4
TBA	PPA9513-6	UC9500 1 Slot 6-Port FC Simplex Front Panel, Empty	32g	8
TBA	PPA9513-6SM	UC9500 1 Slot 6-Port FC Simplex Front Panel with 6 SM adaptors	90g	4
TBA	PPA9513-6MM	UC9500 1 Slot 6-Port FC Simplex Front Panel with 6 MM adaptors	90g	4
TBA	PPA9513-12	UC9500 1 Slot 12-Port FC Simplex Front Panel, Empty	25g	8
TBA	PPA9513-12SM	UC9500 1 Slot 12-Port FC Simplex Front Panel with 12 SM adaptors	142g	4
TBA	PPA9513-12SA	UC9500 1 Slot 12-Port FC Simplex Front Panel with 12 SM APC adaptors	142g	4
TBA	PPA9513-12MM	UC9500 1 Slot 12-Port FC Simplex Front Panel with 12 MM adaptors	142g	4
YFTBP02647	PPST9521-C	UC9500 Splice Tray Cover	29g	1
YFTBP02646	PPST9521-24	UC9500 Splice Tray 24F	43g	2
TBA	PPMT9541-P12	UC9500 Module MTP-Duplex LC 12F G657A2 BendBright Blue Type P	142g	1
TBA	PPMP9541-P12	UC9500 Module MPO-Duplex LC 12F G657A2 BendBright Blue Type P	142g	1
TBA	PPMT9542-P24	UC9500 Module MTP-Duplex LC 24F G657A2 BendBright Blue Type P	142g	1
TBA	PPMP9542-P24	UC9500 Module MPO-Duplex LC 24F G657A2 BendBright Blue Type P	142g	1
TBA	PPMT9561-P12	UC9500 Module MTP-Duplex LC 12F OM3 BendBright Aqua Type P	142g	1
TBA	PPMP9561-P12	UC9500 Module MPO-Duplex LC 12F OM3 BendBright Aqua Type P	142g	1
TBA	PPMT9562-P24	UC9500 Module MTP-Duplex LC 24F OM3 BendBright Aqua Type P	142g	1
TBA	PPMP9562-P24	UC9500 Module MPO-Duplex LC 24F OM3 BendBright Aqua Type P	142g	1
TBA	PPMT9551-P12	UC9500 Module MTP-Duplex LC 12F OM4 BendBright Violet Type P	142g	1
TBA	PPMP9551-P12	UC9500 Module MPO-Duplex LC 12F OM4 BendBright Violet Type P	142g	1
TBA	PPMT9552-P24	UC9500 Module MTP-Duplex LC 24F OM4 BendBright Violet Type P	142g	1
TBA	PPMP9552-P24	UC9500 Module MPO-Duplex LC 24F OM4 BendBright Violet Type P	142g	1

## Enquiries

---

Please contact our local sales office or [mms.asia@prysmiangroup.com](mailto:mms.asia@prysmiangroup.com)

Multimedia Solutions is the data communication portfolio of Prysmian Group and comprises all the necessary portfolio of cable solutions for data communication.

Ask about UC CONNECT for a complete Structure Cabling Solutions with 25 Years System Warranty.

Visit [www.DrakaUC.com](http://www.DrakaUC.com) for more information.

---

© PRYSMIAN GROUP 2019, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.