


## F(6-24)\_CTLS FTL1/M



# **External Underground Central Loosetube Optical Cable**

Cable Design IEC 60794-3-11
ACMA - AS/CA S008



### • Central loose tube construction

- **Tube:** Thermoplastic material, containing up to 24 single-mode optical fibres filled with a low viscosity, thixotropic, non-melting gel fully compatible with fibre coating and tube material.
- Peripheral strength members: Glass fibre reinforced plastic with super-absorbent coating material
- Longitudinal water tightness: Water swellable elements (dry-core)
- Sheath: UV stabilised low smoke, zero halogen, flame retardant compound (LSOH) in compliance with AS 1049. Two ripcords provided beneath the sheath for easy removal

This loose tube dielectric optical cable is designed for external underground installations in ducts by pulling, jetting or floating techniques or by direct burial in open-cut trenches.

#### **Technical data**

Number of Fibres		6 - 12 - 24			
Number of elements		1			
Tube diameter	mm	3.7			
Cable nominal diameter	mm	8.4			
Cable nominal weight	kg/km	73.5			
Max. installation tension	kN	2.0			
Max. crush resistance	kN/100	2.0 (Short term) / 1.0 (Long term)			
Min. bending radius	mm		At full load 180 At no load 90		
Temperature range	°C	Installation -0 -> +50	Transport & Storage -20 -> +	+70 Operation -10 -> +70	

## **Optical Characteristics**

See the attached cabled optical fibre data sheet.

#### **Identification**

### Fibre Colours

I IDIC C	oloui 3											
No.	1	2	3	4	5	6	7	8	9	10	11	12
Colour	blue	orange	green	brown	grey	white	red	black	yellow	violet	pink	aqua
No.	13	14	15	16	17	18	19	20	21	22	23	24
Colour	blue	orange	green	brown	grey	white	red	white	yellow	violet	pink	aqua



<sup>-</sup> Drawing not to scale -



## F(6-24)\_CTLS FTL1/M



#### **Sheath Colour:**

The outer sheath colour is blue.

### **Sheath Marking:**

The outer sheath is marked in 1 meter intervals as follows:

PRYSMIAN DW SM@RTCORE CT Part Number \( \Delta \) N0514 T/N #### MM/YY \*\*\*\*\*M

### Main mechanical characteristics

Parameter	Test method	Test conditions	Acceptance criteria*
Tensile strength	IEC 60794-1-2-E1	Load: As per cable maximum tensile strength in table above.	After 30 minutes the maximum strain on the fibre should not exceed 0.6% and no attenuation increase greater than 0.1 dB occurs
Crush	IEC 60794-1-2-E3	Short time: 10 min Long time: 120 min Load: As per maximum crush resistance in table above Number of positions: 3 adjacent sections (ensuring one over tube and one over lay reversal)	No damage to the sheath or to the core structure and and no attenuation increase greater than 0.1 dB occurs
Impact	IEC 60794-1-2-E4	Weight: 1.5 kg Height: 1.0 m Anvil radius: 12.5 mm Impacts: 1	After 5 minutes no fibre breaks, no damage to the sheath or to the core structure and no attenuation increase greater than 0.1 dB occurs
Torsion	IEC 60794-1-2-E7	Sample length: 1 m Bends: 360° (1turn) clockwise and after measurement (one minute) 720° (2turns) anticlockwise (two minutes)	No fibre breaks, no damage to the sheath or to the core structure and no attenuation increase greater than 0.1 dB occurs
Bend	IEC 60794-1-2-E11	Mandrel diameter: 180 mm Bend: 360° (1turn)	No attenuation increase greater than 0.1 dB occurs
Bend under tension	Concurrent to tensile test IEC 60794-1-2-E18	Mandrel diameter: 360 mm Bend: 360º (1turn)	After 1 minute no fibre breaks, no damage to the sheath or to the core structure and no attenuation increase greater than 0.1 dB occurs from no load to full load
Temperature cycling	IEC 60794-1-2-F1	Sample length: 1000 m (minimum) Temperature range: From - 10 °C to +70 °C	There should be no average attenuation increase at the temperature extremes when compared to the attenuation at ambient temperature. No individual fibre should measure an attenuation greater than 0.15 dB/km
Water penetration * All optical measurer		Sample length=3m, Water height=1m fibres performed at 1550 nm.	No water leakage after 24 hour

## Logistic

### Packing:

New non-returnable timber drums to AS/NZS 2857 with NOLCO-FLEX protection

### **Delivery Lengths:**

Standard delivery length: 4 km with a tolerance of - 1% / + 3%; Drum reference: OF2; Total weight: 430 kg Maximum delivery length: 10 km with a tolerance of - 1% / + 3%; Drum reference: OF5; Total weight: 950 kg

All sizes and values without tolerances are reference values. Specifications are for product as supplied by PrysmianGroup: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PrysmianGroup. The information is believed to be correct at the time of issue. PrysmianGroup reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by PrysmianGroup.



<sup>©</sup> PrysmianGroup 2012, All Rights Reserved