


External Underground Loosetube Optical Cable - Sacrificial Sheath

IEC 60794-3-11

Cable Design

ACMA - AS/CA S008



- Drawing not to scale -

- **Multi-loose tube construction** – Double layer 216 to 624 fibres
- **Central strength member (CSM):** Glass fibre reinforced plastic material (GRP) with or without over-sheathing
- **Tube:** Thermoplastic material, containing 12 or 24 optical fibres filled with a low viscosity, thixotropic, non-melting gel fully compatible with fibre coating and tube material
- **Stranding:** The required numbers of elements (tubes and fillers) are SZ stranded in two layers around the central strength member
- **Longitudinal water tightness:** Water swellable elements (dry-core technology)
- **Sheath:** UV stabilised polyethylene in compliance with AS 1049. Two ripcords provided beneath the sheath for easy removal
- **Hard jacket:** UV stabilised polyamide (Nylon) in compliance with AS 1049 integrally bonded to PE sheath
- **Sacrificial Sheath:** UV stabilised polyethylene in compliance with AS 1049.

This loose tube dielectric optical cable is designed for external underground installations in ducts by pulling, jetting or floating techniques or by direct burial in open-cut trenches.

Technical data

Number of Fibres		216	288	312	624
Number of elements	1 st layer	6	9	10	10
	2 nd layer	12	15	16	16
Tube / Filler diameter	mm	2.1		2.9	
Cable nominal diameter	mm	15.4	16.6	18.4	23.6
Cable nominal weight	kg/km	184	218	268	426
Max. installation tension	kN	2.5		3.0	4.0
Max. crush resistance	kN/100 mm	2.0 (Short term) / 1.0 (Long term)			
Min. bending radius	mm	At full load 20 x Cable OD At no load 10 x Cable OD			
Temperature range	°C	Installation -0 -> +50	Transport & Storage -20 -> +70	Operation -10 -> +70	

Optical Characteristics

See the attached cabled optical fibre data sheet.

Identification

Fibre Colours

No.	1	2	3	4	5	6	7	8	9	10	11	12
Colour	blue	orange	green	brown	grey	white	red	black	yellow	violet	pink	aqua
No.	13	14	15	16	17	18	19	20	21	22	23	24
Colour	blue	orange	green	brown	grey	white	red	white	yellow	violet	pink	aqua

Buffer Tube Colours

No.	1	2	3	4	5	6	7	8	9	10	11	12
Colour	blue	orange	green	brown	grey	white	red	black	yellow	violet	pink	aqua
No.	13	14	15	16	17	18	19	20	21	22	23	24
Colour	blue	orange	green	brown	grey	white	red	white	yellow	violet	pink	aqua
No.	25	26										
Colour	blue	orange										

Tubes 13 and above have one black stripe with the exclusion of tubes 20, 25 & 26 which have one white stripe.

Sheath Colour:

The outer sheath colour is black.

Sheath Marking:

The outer sheath is marked in 1 meter intervals as follows:

PRYSMIAN DW SM@RTCORE SJ Part Number N10514 T/N #### MM/YY MADE IN AUSTRALIA *****

Main mechanical characteristics

Parameter	Test method	Test conditions	Acceptance criteria*
Tensile strength	IEC 60794-1-2-E1	Load: As per cable maximum tensile strength in table above.	After 30 minutes the maximum strain on the fibre should not exceed 0.6% and no attenuation increase greater than 0.1 dB occurs
Crush	IEC 60794-1-2-E3	Short time: 10 min Long time: 120 min Load: As per maximum crush resistance in table above Number of positions: 3 adjacent sections (ensuring one over tube and one over lay reversal)	No damage to the sheath or to the core structure and no attenuation increase greater than 0.1 dB occurs
Impact	IEC 60794-1-2-E4	Weight: 1.5 kg Height: 1.0 m Anvil radius: 12.5 mm Impacts: 1	After 5 minutes no fibre breaks, no damage to the sheath or to the core structure and no attenuation increase greater than 0.1 dB occurs
Torsion	IEC 60794-1-2-E7	Sample length: 1 m Tension: As per table 1 of specification Rotation: a) 180° clockwise, b) return to starting position c) 180° anticlockwise d) return to starting position. Four movements constitute one cycle). Complete 10 cycles (a to d) in one minute maximum	During the final tenth cycle at a) and c) and after completion (no rotation) check transmitting fibres. No fibre breaks, no damage to the sheath or to the core structure and no attenuation increase greater than 0.1 dB occurs
Bend	IEC 60794-1-2-E11	Mandrel diameter: 20 x Cable OD Bend: 360° (1turn)	No attenuation increase greater than 0.1 dB occurs
Bend under tension	Concurrent to tensile test IEC 60794-1-2-E18	Mandrel diameter: 40 x Cable OD Bend: 360° (1turn)	After 1minute no fibre breaks, no damage to the sheath or to the core structure and no attenuation increase greater than 0.1 dB occurs from no load to full load
Temperature cycling	IEC 60794-1-2-F1	Sample length: 1000 m (minimum) Temperature range: From - 10 °C to +70 °C	There should be no average attenuation increase at the temperature extremes when compared to the attenuation at ambient temperature. No individual fibre should measure an attenuation greater than 0.15 dB/km
Water penetration	IEC 60794-1-2-F5B	Sample length=3m, Water height=1m	No water leakage after 24 hour

* All optical measurements for singlemode fibres performed at 1550 nm.

Logistic

Packing:

New non-returnable timber drums to AS/NZS 2857 with NOLCO-FLEX protection

Delivery Lengths:

Standard delivery length is 4 km with a tolerance of - 1% / + 3%

© PrysmianGroup 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by PrysmianGroup: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PrysmianGroup. The information is believed to be correct at the time of issue. PrysmianGroup reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by PrysmianGroup.