




MEDIUM VOLTAGE CABLES

Aluminium 19/33 kV - Three core heavy duty screened unarmoured





Application

Electricity distribution or sub-transmission networks cable typically used as primary supply to Commercial, Industrial and urban residential networks. Suitable for high fault level systems rated up to 10kA/1sec. Higher fault current rated constructions are available on request.

Approvals

Approved by all major power Utilities and industrial customers in Australia.

Behaviour in flame and fire:

PVC or LSOH outer sheath exceeds the requirements of IEC 60332-1.

Temperature range

Minimum installation temperature: 0 °C Maximum operating temperature: +90 °C Minimum operating temperature: -25 °C

Minimum bending radius

Installed cables: 12D (PVC only)

15D (HDPE)

During installation: 18D (PVC only)

25D (HDPE)

Resistance to

Chemical exposure: Accidental Mechanical impact: Light (PVC only)

Heavy (HDPE)

Water exposure: XLPE - Spray

EPR - Immersion/Temporary coverage

Solar radiation and

weather exposure: Suitable for direct exposure.

Cable design

Conductor:

Circular compacted aluminium

Conductor screen:

Extruded semi-conductive compound, bonded to the insulation and applied in the same operations as the insulation.

Insulation:

Cross Linked Polyethylene (XLPE) – standard Ethylene Propylene Rubber (EPR) – alternative

Insulation screen:

Extruded, semi-conductive compound

Metallic screen:

Plain annealed copper wire: nominal 10kA for 1 second. See table next page.

Sheath:

Black 5V-90 polyvinyl chloride (PVC) – standard Orange 5V-90 PVC inner plus black high density polyethylene (HDPE) outer – alternative Low smoke zero halogen (LSOH) – alternative

Installation conditions

In free air In duct In trench

In ground with protection





All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.

MEDIUM VOLTAGE CABLES

Physical & Electrical Characteristics

			Aluminium	19/33 kV - Th	ree core heav	y duty screer	ned unarmour	ed		
Product of	code: 3CALX33H	ID	,	.5,55		, 441, 50.00.				
Nominal conductor area mm²		50	70	95	120	150	185	240	300	
Nominal conductor diameter mm		8.1	9.8	11.5	12.9	14.2	16.0	18.1	20.6	
Nominal insulation thickness mm		8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	
Approx cable diameter mm		68.6	72.4	76.3	79.4	82.5	86.5	91.5	97.6	
Approx mass kg/100m		355	410	470	520	565	630	715	820	
Max pulling tension on conductors kN		7.5	11	14	18	23	25	25	25	
Max pulling tension on stocking grip kN		7.5	11	14	18	23	25	25	25	
Min bending radius* during installation mm		1230	1300	1370	1430	1490	1560	1650	1760	
Min bending radius* set in position mm		820	870	920	950	990	1040	1100	1170	
Max conductor resistance, dc @ 20°C Ohm/km		0.641	0.443	0.320	0.253	0.206	0.164	0.125	0.100	
Conductor resistance, ac @ 90°C & 50 Hz Ohm/km		0.822	0.568	0.411	0.325	0.265	0.211	0.161	0.130	
Inductance mH/km		0.457	0.422	0.401	0.387	0.375	0.359	0.345	0.332	
Inductive reactance, @ 50Hz Ohm/km		0.144	0.133	0.126	0.121	0.118	0.113	0.108	0.104	
Zero seq. impedance @ 20°C & 50 Hz Ohm/km		2.46+ j0.0981	1.76+ j0.0871	1.28+ j0.0805	1.09+ j0.0762	1.05+ j0.0724	1.01+ j0.0674	0.967+ j0.0632	0.942+ j0.0593	
Capacitance, phase to earth µF/km		0.139	0.155	0.171	0.183	0.196	0.211	0.231	0.255	
Min insulation resistance @ 20°C MOhm.km		18,000	16,000	15,000	14,000	13,000	12,000	11,000	9,900	
Electric stress at conductor screen kV/mm		4.08	3.85	3.67	3.56	3.46	3.36	3.26	3.16	
Charging current @ rated voltage & 50 Hz A/phase/km		0.831	0.927	1.02	1.09	1.17	1.26	1.38	1.52	
Short circuit rating	Phase conductor kA,1 sec	4.7	6.6	9.0	11.3	14.2	17.5	22.7	28.3	
	Metallic screen kA,1sec	4.6	6.3	8.6	10	10	10	10	10	
Continuous current rating	In ground, direct buried A	145	190	225	255	285	320	380	428	
	In ground, in singleway ducts A	130	160	195	225	250	280	314	354	
	In free air, unenclosed & spaced from wall A	150	185	235	270	305	350	430	491	

The cables described are designed to be used for the supply of electrical energy in fixed applications up to the rated voltages at a nominal power frequency between 49Hz and 61Hz. All values are for XLPE cables only. *Increased radius required for HDPE and nylon incorporating designs.