


MEDIUM VOLTAGE CABLES

Copper 12.7/22 kV – Single core light duty screened unarmoured



Application

Electricity distribution network cable typically used as primary supply to Commercial, Industrial and urban residential networks. Suitable for low fault level or fast fault clearing cable systems.

Approvals

Approved by all major power Utilities and industrial customers in Australia.

Behaviour in flame and fire:

PVC or LSOH outer sheath exceeds the requirements of IEC 60332-1.

Temperature range

Minimum installation temperature: 0 °C
 Maximum operating temperature: +90 °C
 Minimum operating temperature: -25 °C

Minimum bending radius

Installed cables: 12D (PVC only)
 15D (HDPE)
 During installation: 18D (PVC only)
 25D (HDPE)

Resistance to

Chemical exposure: Accidental
 Mechanical impact: Light (PVC only)
 Heavy (HDPE)
 Water exposure: XLPE – Spray
 EPR – Immersion/Temporary coverage
 Solar radiation and weather exposure: Suitable for direct exposure.

Cable design

Conductor:
 Plain circular compacted copper

Conductor screen:
 Extruded semi-conductive compound, bonded to the insulation and applied in the same operations as the insulation.

Insulation:
 Cross Linked Polyethylene (XLPE) – standard
 Ethylene Propylene Rubber (EPR) – alternative

Insulation screen:
 Extruded, semi-conductive compound

Metallic screen:
 Plain annealed copper wire: nominal 3kA for 1 second.
 See table next page.

Sheath:
 Black 5V-90 polyvinyl chloride (PVC) – standard
 Orange 5V-90 PVC inner plus black high density polyethylene (HDPE) outer – alternative
 Low smoke zero halogen (LSOH) – alternative

Installation conditions

In free air
 In duct
 In trench
 In ground with protection

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.



MEDIUM VOLTAGE CABLES

Physical & Electrical Characteristics

Copper 12.7/22 kV – Single core light duty screened unarmoured													
Product code: 1CCUX22LD													
Nominal conductor area mm ²	35	50	70	95	120	150	185	240	300	400	500	630	
Nominal conductor diameter mm	7.0	8.2	9.8	11.5	12.9	14.3	16.1	18.2	20.6	23.5	26.6	30.3	
Nominal insulation thickness mm	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	
Approx cable diameter mm	26.6	27.7	29.5	31.2	32.8	34.2	36.2	38.4	41.1	44.8	48.1	52.0	
Approx mass kg/100m	100	115	140	165	195	225	265	320	385	475	585	725	
Max pulling tension on conductor kN	2.5	3.5	4.9	6.7	8.4	11	13	17	21	25	25	25	
Max pulling tension on stocking grip kN	2.5	2.7	3.1	3.4	3.8	4.1	4.6	5.2	5.9	7.0	8.1	9.4	
Min bending radius* during installation mm	480	500	530	560	590	620	650	690	740	810	860	940	
Min bending radius* set in position mm	320	330	350	370	390	410	430	460	490	540	580	620	
Max conductor resistance, dc @ 20°C Ohm/km	0.524	0.387	0.268	0.193	0.153	0.124	0.0991	0.0754	0.0601	0.0470	0.0366	0.0283	
Conductor resistance, ac @ 90°C & 50 Hz Ohm/km	0.668	0.494	0.342	0.247	0.196	0.159	0.128	0.0978	0.0788	0.0628	0.0504	0.0410	
Inductance, trefoil touching mH/km	0.492	0.470	0.435	0.414	0.397	0.384	0.372	0.357	0.346	0.335	0.324	0.315	
Inductive reactance, trefoil touching @ 50Hz Ohm/km	0.155	0.148	0.137	0.130	0.125	0.121	0.117	0.112	0.109	0.105	0.102	0.0988	
Zero seq. impedance @ 20°C & 50 Hz Ohm/km	1.46+ j0.0913	1.32+ j0.0851	1.20+ j0.0751	1.13+ j0.0693	1.09+ j0.0645	1.06+ j0.0611	1.03+ j0.0575	1.01+ j0.0538	0.995+ j0.0509	0.982+ j0.0481	0.973+ j0.0451	0.965+ j0.0426	
Capacitance, phase to earth µF/km	0.164	0.179	0.200	0.223	0.241	0.259	0.282	0.310	0.343	0.386	0.426	0.473	
Min insulation resistance @ 20°C MOhm.km	16,000	14,000	13,000	11,000	10,000	9,700	8,900	8,100	7,300	6,500	5,900	5,300	
Electric stress at conductor screen kV/mm	3.64	3.49	3.33	3.21	3.12	3.06	2.99	2.91	2.85	2.78	2.73	2.68	
Charging current @ rated voltage & 50 Hz A/phase/km	0.652	0.713	0.799	0.888	0.961	1.03	1.12	1.24	1.37	1.54	1.70	1.89	
Short circuit rating	Phase conductor kA, 1 sec	5.0	7.2	10.0	13.6	17.2	21.5	26.5	34.3	42.9	57.2	71.5	90.1
	Metallic screen kA, 1 sec	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
Continuous current rating	In ground, direct buried A	175	205	250	300	335	375	425	490	550	625	705	790
	In ground, in singleway ducts A	170	200	245	290	325	360	405	460	515	580	650	730
	In free air, unenclosed & spaced from wall A	180	215	270	325	375	425	490	575	660	765	880	1005

The cables described are designed to be used for the supply of electrical energy in fixed applications up to the rated voltages at a nominal power frequency between 49Hz and 61Hz. All values are for XLPE cables only. *Increased radius required for HDPE and nylon incorporating designs.