


MEDIUM VOLTAGE CABLES
Copper 6.35/11 kV – Three core light duty screened unarmoured

Application

Electricity distribution network cable typically used as primary supply to Commercial, Industrial and urban residential networks. Suitable for low fault level or fast fault clearing cable systems.

Approvals

Approved by all major power Utilities and industrial customers in Australia.

Behaviour in flame and fire:

PVC or LSOH outer sheath exceeds the requirements of IEC 60332-1.

Temperature range

Minimum installation temperature: 0 °C
 Maximum operating temperature: +90 °C
 Minimum operating temperature: -25 °C

Minimum bending radius

Installed cables: 12D (PVC only)
 15D (HDPE)
 During installation: 18D (PVC only)
 25D (HDPE)

Resistance to

Chemical exposure: Accidental
 Mechanical impact: Light (PVC only)
 Heavy (HDPE)
 Water exposure: XLPE – Spray
 EPR – Immersion/Temporary coverage
 Solar radiation and weather exposure: Suitable for direct exposure.

Cable design

Conductor:
 Plain circular compacted copper

Conductor screen:
 Extruded semi-conductive compound, bonded to the insulation and applied in the same operations as the insulation.

Insulation:
 Cross Linked Polyethylene (XLPE) – standard
 Ethylene Propylene Rubber (EPR) – alternative

Insulation screen:
 Extruded, semi-conductive compound

Metallic screen:
 Plain annealed copper wire: nominal 3kA for 1 second.
 See table next page.

Sheath:
 Black 5V-90 polyvinyl chloride (PVC) – standard
 Orange 5V-90 PVC inner plus black high density polyethylene (HDPE) outer – alternative
 Low smoke zero halogen (LSOH) – alternative

Installation conditions

In free air
 In duct
 In trench
 In ground with protection

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.



MEDIUM VOLTAGE CABLES

Physical & Electrical Characteristics

Copper 6.35/11 kV – Three core light duty screened unarmoured											
Product code: 3CCUX11LD											
Nominal conductor area mm ²	25	35	50	70	95	120	150	185	240	300	
Nominal conductor diameter mm	6.1	7.0	8.2	9.8	11.5	12.9	14.3	16.1	18.2	20.6	
Nominal insulation thickness mm	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	
Approx cable diameter mm	42.6	44.6	47.3	51.2	55.1	58.3	61.5	65.5	70.6	76.3	
Approx mass kg/100m	195	230	270	345	440	520	610	730	915	1110	
Max pulling tension on conductors kN	5.3	7.4	11	15	20	25	25	25	25	25	
Max pulling tension on stocking grip kN	5.3	7.0	7.8	9.2	11	12	13	15	17	20	
Min bending radius* during installation mm	770	800	850	920	990	1050	1110	1180	1270	1370	
Min bending radius* set in position mm	510	540	570	610	660	700	740	790	850	920	
Max conductor resistance, dc @ 20°C Ohm/km	0.727	0.524	0.387	0.268	0.193	0.153	0.124	0.0991	0.0754	0.0601	
Conductor resistance, ac @ 90°C & 50 Hz Ohm/km	0.927	0.668	0.494	0.342	0.247	0.196	0.159	0.128	0.0984	0.0796	
Inductance mH/km	0.415	0.397	0.379	0.350	0.333	0.319	0.310	0.300	0.290	0.282	
Inductive reactance, @ 50Hz Ohm/km	0.130	0.125	0.119	0.110	0.105	0.100	0.0973	0.0942	0.0910	0.0885	
Zero seq. impedance @ 20°C & 50 Hz Ohm/km	3.46+ j0.0836	3.26+ j0.0781	3.12+ j0.0726	2.79+ j0.0635	2.54+ j0.0585	2.34+ j0.0543	2.17+ j0.0515	2.03+ j0.0485	1.90+ j0.0454	1.70+ j0.0431	
Capacitance, phase to earth µF/km	0.212	0.231	0.255	0.290	0.325	0.354	0.383	0.419	0.465	0.518	
Min insulation resistance @ 20°C MOhm.km	12,000	11,000	10,000	8,900	7,900	7,200	6,600	6,000	5,400	4,900	
Electric stress at conductor screen kV/mm	2.64	2.56	2.49	2.40	2.33	2.29	2.25	2.22	2.18	2.14	
Charging current @ rated voltage & 50 Hz A/phase/km	0.422	0.461	0.509	0.578	0.648	0.706	0.764	0.837	0.927	1.03	
Short circuit rating	Phase conductor kA, 1 sec	3.6	5.0	7.2	10.0	13.6	17.2	21.5	26.5	34.3	42.9
	Metallic screen kA, 1 sec	3.0	3.0	3.0	3.3	3.5	3.8	4.0	4.3	4.6	5.1
Continuous current rating	In ground, direct buried A	140	165	195	235	280	325	365	410	475	530
	In ground, in singleway ducts A	120	145	170	205	240	280	310	350	405	455
	In free air, unenclosed & spaced from wall A	135	160	190	235	285	330	380	435	510	580

The cables described are designed to be used for the supply of electrical energy in fixed applications up to the rated voltages at a nominal power frequency between 49Hz and 61Hz. All values are for XLPE cables only. *Increased radius required for HDPE and nylon incorporating designs.